

photomultiplier HV Base

HV130K20CP series data sheet

1 description

The HV130K20CP is a compact photomultiplier positive polarity HV Base operating from a low voltage supply (+5 to +15 V). It incorporates a CW multiplier that directly supplies voltages to the photomultiplier electrodes. The HV Base is intended for use with 10-stage, 130 mm diameter capped photomultipliers for applications requiring up to +2000 volts and ac coupling.

The unit is housed in a screened cylindrical metal enclosure, the diameter of which is compatible with the photomultiplier overcap. Threaded mounting bushes are provided. The anode output is via a 0.5 m length of shielded RG174U cable.

The photomultiplier operating voltage is set using any one of three programming options as shown in section 8.

2 applications

The HV130K20CP is designed for use in the following photomultiplier operating modes:

- pulsed light
- photon counting

3 features

- low power consumption
- compact
- no high voltage cables
- low noise
- linearity limited only by photomultiplier performance

4 specifications

at HV = 1000V	unit	min	typ	max
supply voltage	V	+5		+15
control voltage	V	+0.1		+2
output high voltage	V	+100		+2000
output (anode) current	μ A			200*
supply current at +5 V;				
for anode current = 0 μ A	mA		1.5	
for anode current = 100 μ A	mA		6.5	
supply current at +12 V:				
for anode current = 0 μ A	mA		1	
for anode current = 100 μ A	mA		5	
line regulation	%/V			0.01
anode load regulation:				
for anode current 0 - 100 μ A	%			0.01
temperature coefficient	%/ $^{\circ}$ C			0.02
switch-on time (10 - 90%)	s		0.2	
switch-off time (90 - 10%)	s		55	
no pmt				
anode ripple:				
with 10 k Ω 20 pF load	mV(p-p)		2	
weight	g		60	


*subject to photomultiplier limit



5 ratings


	unit	min	typ	max
supply voltage	V	4.5		18
control voltage	V	0		3
temperature (operating): at 93% RH, non-condensing	$^{\circ}$ C	-40		60

6 schematic diagram






7 voltage distribution

The photomultiplier pin configuration for this HV Base is given below. The voltage distribution for an applied HV of V volts is shown in the table. Note that an anode load resistor (R_L) of 100 K Ω is included. A 10 M Ω safety resistor and capacitor, C, are connected between anode and ground to maintain the output at 0V.



k	d ₁	d ₂	...	d ₉	d ₁₀	a
6/16V	1/16V	1/16V		1/16V	1/16V	

8 programming options




9 dimensions and photomultiplier options

The HV301K20CP series HV base can be used with the following photomultipliers:

9390KB, 9490KB

all dimensions in mm




10 linearity

Linearity performance is dependent on the particular photomultiplier being used with the HV Base. It is measured as the % deviation in either peak pulse current, or average current, depending on the mode of operation.

Please refer to the corresponding photomultiplier data sheet for further information.

11 output configurations

The photomultiplier anode is internally ac coupled to ground via a 10 MΩ safety resistor. An internal load resistor, R_L (int), of 100 KΩ is also provided. An external load resistor, R_L , can be added if required.



C = internal coupling capacitor
 R_L (int) = internal load resistor
 R_L = external load resistor (optional)

12 ordering information

item	ordering code
without flange	HV130K20CP
with flange	HV130K20CPF

13 warning

High voltages generated by these products present an electrical shock hazard and appropriate precautions must be taken.

Installation must be by qualified personnel.

All units are despatched with the internal potentiometer set to zero.

Do not operate outside the quoted ratings of the HV130K20CP or those of the photomultiplier. This may result in loss of performance, permanent damage, or both.

ET Enterprises Limited
45 Riverside Way
Uxbridge UB8 2YF
United Kingdom
tel: +44 (0) 1895 200880
fax: +44 (0) 1895 270873
e-mail: sales@et-enterprises.com
web site: www.et-enterprises.com

ADIT Electron Tubes
300 Crane Street
Sweetwater TX 79556 USA
tel: (325) 235 1418
toll free: (800) 399 4557
fax: (325) 235 2872
e-mail: sales@electron tubes.com
web site: www.electrontubes.com

an ISO 9001 and ISO 14001 registered company

The company reserves the right to modify these designs and specifications without notice. Developmental devices are intended for evaluation and no obligation is assumed for future manufacture. While every effort is made to ensure accuracy of published information the company cannot be held responsible for errors or consequences arising therefrom.

ET Enterprises
electron tubes

© ET Enterprises Ltd, 2014
DS_HV130K20CP Issue 1 (27/03/14)